


Pressure/Vacuum Diaphragm Valve

with internal coating
Deflagration-proof and Endurance Burning-proof

PROTEGO® UB/SF-IIA1



with freeze resistant water glycol mixture, which assures safe operation under extreme cold weather conditions. The liquid is capsuled and is not discharged or diluted during operation. The valve can also be operated at temperatures lower than 0°C without ice constricting the funktion of the valve.

When the pressure in the tank reaches the set pressure, the FPM-diaphragm (1) on the outer valve seat ring (2) is lifted and vapours vent to the environment. The set pressure is adjusted by the liquid (glycol water mixture) column height, which is filled into the outer ring chamber (3). The overpressure chamber is equipped with an opening (4) to keep the pressure in balance with the ambient pressure. If a vacuum builds up in the tank, it is transmitted through pressure balancing tubes into the vacuum chamber (5) (inner chamber). If the set vacuum, which depends on the liquid column height in the vacuum chamber, is reached the atmospheric pressure lifts the diaphragm up off the inner valve seat ring (6). Ambient air can now flow into the tank. The liquid column heights, which affect the set pressures and vacuum, can be checked by floating level indicators (7).

The tank pressure is maintained up to the set pressure with a tightness that is far superior to the conventional standard due to our highly developed manufacturing technology. This is achieved because the liquid loaded diaphragm presses tightly around the special designed valve seat surface area, even when the operating pressure increases. This is extremely important to reduce leakage to an absolute minimum. After the excess pressure or vacuum is discharged, the valve reseats and provides a tight seal.

If the tank pressure exceeds the adjusted set pressure, as the case may be explosive gas/product-vapour air mixtures exit. The speed at which these mixtures exit the annular gap between the diaphragm and the outer valve seat ring while overcoming the set pressure is much faster than the flame speed. If this mixture ignites, flashback into the tank is prevented. If the mixture flow continues, the dynamic flame arresting feature prevents flashback ignition even in the case of endurance burning. Even at relatively low flow rates, which occur during thermal outbreathing, the gap formed by the volumetric flow is so narrow that flames are extinguished in the gap and flashback is prevented.

The PROTEGO® UB/SF-IIA1 valve is available for substances of explosion group IIA1 - methane. The valve can be used up to an operating temperature of +60°C / 140°F and an operating pressure up to ≥3.5 mbar / 1.4 inch W.C. and meets the requirements of European tank design standard EN 14015 – Appendix L and API 2000

Type-approved according to ATEX Directive and EN ISO 16852 as well as other international standards.

Settings:

| | | | |
|------------------|--------|----------------|-----------------------|
| pressure: | DN 80 | +3.5 mbar | up to +50 mbar |
| | | +1.4 inch W.C. | up to +20 inch W.C. |
| | DN 100 | +3,5 mbar | up to +45 mbar |
| | | +1.4 inch W.C. | up to +18 inch W.C. |
| | DN 150 | +3,5 mbar | up to +46 mbar |
| | | +1.4 inch W.C. | up to +18.4 inch W.C. |

Higher pressure settings up to +150 mbar (60 inch W.C.) in special design with additional liquid reservoir upon request.

| | | |
|----------------|----------------|---------------------|
| vacuum: | -3,5 mbar | up to -35 mbar |
| | -1.4 inch W.C. | up to -14 inch W.C. |

Function and Description

It is a highly developed combined pressure and vacuum valve with dynamic and static flame arrester.

The deflagration- and endurance burning-proof PROTEGO® UB/SF-IIA1 type diaphragm valve is a highly developed combined pressure and vacuum valve with dynamic flame arrester. Worldwide this design is unique. It is primarily used within biogas plants as a safety device for flame transmission proof in- and outbreathing on tanks, containers and process engineering apparatus. The valve offers reliable protection against excess pressure and vacuum, prevents the inbreathing of air and product losses almost up to the set pressure and protects against atmospheric deflagration and endurance burning if stabilized burning occurs. The set pressure is adjusted

Special Features and Advantages

- high performance seal reducing product loss below EPA's 500ppm rule preventing environmental pollution
- set pressure close to opening pressure enables optimum pressure maintenance in the system
- can be used as a protective system according to ATEX directive in areas subject to an explosion hazard
- protection against atmospheric deflagrations and endurance burning for products up to explosion group IIA1
- flame-transmission-proof venting of the pressure chamber
- freeze protection at sub-zero conditions
- self draining function for condensate
- liquid column height is monitored by level indicators
- easy maintenance through hinged vent cap
- the modular design enables individual diaphragm to be replaced
- can be applied in biogas plants due to internal coating
- permanent refilling of the frost-proof liquid is not necessary, liquid remains within the valve chambers
- spray nozzle for internal cleaning and avoidance of foam upon request

Design Types and Specifications

Almost any combination of vacuum and pressure settings can be utilized for the valve. The diaphragm is pressurized by liquid. Higher pressures can be achieved upon request with a special liquid reservoir.

There are two different designs:

Pressure/vacuum diaphragm valve, basic design **UB/SF-**

Pressure/vacuum diaphragm valve with heating coil **UB/SF-**
(max. heating fluid temperature +85°C / 185°F)

Remark

$$\text{set pressure} = \frac{\text{opening pressure resp. tank design pressure}}{1 + \frac{\text{overpressure \%}}{100\%}}$$

The set pressures have to be chosen depending on the pressure increase (e.g. 40% or 100% pressure increase from set pressure to opening pressure at which the required valve performance is reached). For reaching a higher valve performance the valve can be designed with a pressure increase of 100% at accordingly reduced valve set pressure.

Set pressure = the valve starts to open

Opening pressure = set pressure plus overpressure

Overpressure % = percentage pressure increase over the set pressure

Table 1: Dimensions

Dimensions in mm / inches

To select the nominal size (DN), please use the flow capacity charts on the following page.

| DN | pressure | 80 / 3" | pressure | 100 / 4" | pressure | 150 / 6" |
|----|----------------------------------|-------------|----------------------------------|-------------|--------------------------------|-------------|
| a | up to +28 mbar / +11.2 inch W.C. | 615 / 24.21 | up to +28 mbar / +11.2 inch W.C. | 645 / 25.39 | up to +25 mbar / +10 inch W.C. | 680 / 26.77 |
| a | > +28 mbar / +11.2 inch W.C. | 765 / 30.12 | > +28 mbar / +11.2 inch W.C. | 795 / 31.30 | > +25 mbar / +10 inch W.C. | 830 / 32.68 |
| b | | 410 / 16.14 | | 485 / 19.09 | | 590 / 23.23 |

Pressure settings > +50 mbar / +20 inch W.C. (DN 80), > +45 mbar / +18 inch W.C. (DN 100), > +46 mbar / +18.4 inch W.C. (DN150) with additional liquid reservoir - dimensions upon request.


Dimensions for pressure/vacuum diaphragm valves with heating coil upon request.

Table 2: Selection of explosion group

| MESG | Expl. Gr. (IEC/CEN) | Special approvals upon request. |
|-----------|---------------------|---------------------------------|
| ≥ 1.14 mm | IIA1 | |



for safety and environment



Pressure/Vacuum Diaphragm Valve

with internal coating
Deflagration-proof and Endurance Burning-proof

PROTEGO® UB/SF-IIA1

Table 3: Material for housing


| | |
|------------------------------|-------------------------------|
| Design | B |
| Housing | Steel |
| Coating of housing | 2 components polymere coating |
| Valve top | Stainless Steel |
| Heating coil (UB/SF-H-...-I) | Stainless Steel |
| Valve seats | Stainless Steel |
| Gasket | FPM |
| Diaphragm | FPM |

Special materials upon request.

Table 4: Flange connection type

| |
|-------------------------|
| EN 1092-1, Form B1 |
| ASME B 16.5 CL 150 R.F. |



Other types upon request.



Pressure/Vacuum Diaphragm Valve

Flow Capacity Charts


PROTEGO® UB/SF-IIA1



The flow capacity charts have been determined with a calibrated and TÜV certified flow capacity test rig.
 Volume flow \dot{V} in (m³/h) and CFH refer to the standard reference conditions of air in ISO 6358 (20°C, 1bar).
 For conversion to other densities and temperatures, refer to Sec. 1: "Technical Fundamentals."





for safety and environment




Pressure/Vacuum Diaphragm Valve

Flow Capacity Charts

PROTEGO® UB/SF-IIA1



The flow capacity charts have been determined with a calibrated and TÜV certified flow capacity test rig. Volume flow \dot{V} in (m³/h) and CFH refer to the standard reference conditions of air in ISO 6358 (20°C, 1bar). For conversion to other densities and temperatures, refer to Sec. 1: "Technical Fundamentals."



Pressure/Vacuum Diaphragm Valve

Flow Capacity Charts

PROTEGO® UB/SF-IIA1

